

Ri-Mark Platinum

#	code	Reference	colour	Pantone	RAL	Avery 700	Mactac 9800 Pro	Oracal 551	Metamark M7	Avery 800	Oracal 751C
1	12593	Ri-Mark Platinum P 804 Pastel Yellow		± 131 C	± 1016	-	= 9809-21	-	-	-	-
2	12507	Ri-Mark Platinum P 805 Yellow		± 108 C	± 1018	± 707	= 9807-43	-	M7-136	807 PC	-
3	12508	Ri-Mark Platinum P 806 Bright Yellow *K+AF		± 109 C	± 1021	± 739	= 9809-46	= 202	-	-	o22
4	12509	Ri-Mark Platinum P 807 Sun Yellow *K+AF		± 7548 C	± 1023	= 706	= 9809-45	-	M7-131	806 PC	211
5	12510	Ri-Mark Platinum P 808 Dark Yellow		± 3514 C	± 1003	= 704	± 9809-47	= 229	M7-132	856 PC	-
6	12572	Ri-Mark Platinum P 809 Saffran		± 137 C	± 1028	± 764	= 9809-11	= 215	M7-137	-	-
7	12573	Ri-Mark Platinum P 810 Light Orange		± 151 C	± 3003	-	= 9801-44	= 395	M7-138	-	-
8	12511	Ri-Mark Platinum P 811 Orange		± 1505 C	± 2003	-	-	= 35	-	-	o35
9	12512	Ri-Mark Platinum P 812 Carrot *K+AF		± 1585 C	± 2008	= 705	± 9801-40	-	M7-133	805 PC	332
10	12574	Ri-Mark Platinum P 813 Poppy Red		± 179 C	-	± 743	= 9859-10	± 302	-	-	-
11	12513	Ri-Mark Platinum P 814 Vivid red		± 3556 C	± 3020	= 737	= 9859-47	± 303	-	-	-
12	12514	Ri-Mark Platinum P 815 Tomato Red		± 485 C	± 3020	± 749-02	= 9859-46	-	M7-141	-	o32
13	12515	Ri-Mark Platinum P 816 Spicy Red *K+AF		± 3546 C	± 3020	= 765-01	= 9859-43	= 397	M7-142	826 PC	-
14	12516	Ri-Mark Platinum P 817 Medium Red *K+AF		± 3517 C	± 3000	= 749-01	= 9859-00	= 305	-	803 PC	-
15	12518	Ri-Mark Platinum P 818 Dark Red		± 3517 C	± 3001	= 703	= 9859-12	= 306	M7-148	-	306
16	12575	Ri-Mark Platinum P 819 Red *K+AF		± 7621 C	± 3002	-	-	± 31	-	-	-
17	12576	Ri-Mark Platinum P 820 Wine Red *K+AF		± 7623 C	± 3003	= 778	= 9859-41	± 307	M7-114	-	-
18	12577	Ri-Mark Platinum P 821 Burgundy		± 209 C	± 3004	± 702	= 9859-05	± 308	M7-145	863 PC	-
19	12578	Ri-Mark Platinum P 822 Rioja Red		± 504 C	± 3005	± 702	= 9859-28	-	-	-	-
20	12519	Ri-Mark Platinum P 823 Process Magenta		± 214 C	-	± 715	-	-	M7-182	-	-
21	12520	Ri-Mark Platinum P 824 Plum		± 520 C	-	± 777	-	-	-	-	-
22	12579	Ri-Mark Platinum P 825 Aubergine		± 525 C	-	-	= 9839-38	-	-	-	-
23	12580	Ri-Mark Platinum P 826 Violet		± 268 C	-	± 717	= 9839-13	= 403	M7-183	-	-
24	12581	Ri-Mark Platinum P 827 Midnight Blue		± 2767 C	± 5011	± 724-01	= 9839-19	= 513	M7-185	-	588
25	12522	Ri-Mark Platinum P 828 Abyss Blue		± 2768 C	-	= 724	= 9839-40	-	-	-	518
26	12523	Ri-Mark Platinum P 829 Old Blue		± 281 C	-	= 738	± 9839-23	± 50	M7-119	-	591
27	12526	Ri-Mark Platinum P 830 Dark Blue		± 2748 C	-	± 723	-	= 164	M7-156	823 PC	537
28	12528	Ri-Mark Platinum P 832 Marine Blue		± 288 C	± 5002	± 792	± 9839-12	± 511	-	-	-
29	12529	Ri-Mark Platinum P 833 Ultramarine Blue *K+AF		± 2748 C	± 5002	± 747	± 9839-12	= 511	M7-117	847 PC	o65
30	12530	Ri-Mark Platinum P 834 Reflex Blue *K+AF		± 287 C	-	± 752	= 9839-26	± 510	M7-118	-	510
31	12531	Ri-Mark Platinum P 835 Cosmos Blue		± 2145 C	± 5005	= 708	= 9839-11	± 57	M7-154	808 PC	-
32	12534	Ri-Mark Platinum P 836 Permanent Blue		± 2935 C	-	= 741	9839-22	= 166	M7-153	841 PC	o51
33	12582	Ri-Mark Platinum P 837 Medium Blue		± 2175 C	-	= 751	9839-24	= 52	-	-	o52
34	12541	Ri-Mark Platinum P 838 Ocean Blue		± 3005 C	-	= 709	-	= 167	-	809 PC	-
35	12542	Ri-Mark Platinum P 839 Olympic Blue *K+AF		± 2194 C	-	= 784	= 9839-10	± 505	M7-151	-	-
36	12583	Ri-Mark Platinum P 840 Light Blue		± 2915 C	-	± 732	= 9839-07	± 504	M7-150	-	-
37	12584	Ri-Mark Platinum P 841 Petrol *K+AF		± 321 C	± 5018	= 731	= 9849-17	= 503	M7-165	831 PC	o66
38	12585	Ri-Mark Platinum P 842 Dark Petrol		± 315 C	-	± 798	= 9849-26	= 608	-	-	608
39	12586	Ri-Mark Platinum P 843 Dark Lagoon		± 548 C	-	-	= 9849-34	-	M7-168	-	-
40	12540	Ri-Mark Platinum P 844 Forest Green		± 343 C	-	-	-	-	-	-	-
41	12587	Ri-Mark Platinum P 845 Dark Green		± 3298 C	-	= 711	= 9849-51	= 60	M7-164	811 PC	661
42	12588	Ri-Mark Platinum P 846 Freedom Green *K+AF		± 341 C	± 6029	= 756	= 9849-10	± 604	M7-163	834 PC	o68
43	12544	Ri-Mark Platinum P 847 Medium Green		± 340 C	± 6024	-	= 9849-52	± 603	M7-162	812 PC	619
44	12545	Ri-Mark Platinum P 848 Bright Green		± 354 C	± -	-	= 9849-36	-	M7-197	-	-
45	12546	Ri-Mark Platinum P 849 Grass Green *K+AF		± 361 C	± 6018	= 713	± 9849-55	= 602	M7-161	-	o64
46	12589	Ri-Mark Platinum P 850 Apple Green *K+AF		± 7488 C	-	= 714	= 9849-13	= 601	M7-160	814 PC	o63
47	12590	Ri-Mark Platinum P 851 Yellow Green		± 2299 C	-	± 714-02	= 9849-54	-	M7-198	-	-
48	12547	Ri-Mark Platinum P 852 Light Beige		± 468 C	± 1015	± 758	± 9829-05	± 841	M7-172	-	-
49	12548	Ri-Mark Platinum P 853 Chocolate Brown		± 4625 C	± 8007	± 718	± 9883-06	-	-	-	-
50	12549	Ri-Mark Platinum P 854 Dark Brown		± 7533 C	± 8017	= 762	± 9383-04	= 803	-	880 PC	o80
51	12550	Ri-Mark Platinum P 801 Black		± Black C	± 9005	= 701	= 9889-00	= 701	M7-110	801 PC	70
52	12591	Ri-Mark Platinum P 855 Mystic Grey *K+AF		± 433 C	± 7021	= 759-01	= 9889-17	-	M7-126	-	720
53	12551	Ri-Mark Platinum P 856 Anthracite *K+AF		-	-	= 746	= 9889-01	= 93	M7-196	895 PC	o93
54	12552	Ri-Mark Platinum P 857 Traffic Grey *K+AF		± 446 C	-	= 759-02	= 9889-05	= 714	M7-128	881 PC	-
55	12553	Ri-Mark Platinum P 858 Dark Grey *K+AF		± 445 C	± 7012	± 720	= 9889-02	= 713	M7-124	820 PC	713
56	12554	Ri-Mark Platinum P 859 Medium Grey		± 431 C	-	-	-	-	-	-	-
57	12555	Ri-Mark Platinum P 860 Slate Grey *K+AF		± 444 C	± 7000	= 725	= 9889-15	± 756	-	825 PC	721
58	12728	Ri-Mark Platinum P 868 Light Grey		± 443 C	± 7042	-	= 9889-03	± 712	M7-123	844 PC	-
59	12556	Ri-Mark Platinum P 861 Grey		± 429 C	± 7040	-	± 9889-14	-	-	-	-
60	12557	Ri-Mark Platinum P 862 Pearl Grey		± 427 C	± 7035	= 745	± 9889-04	= 72	M7-122	859 PC	o720
61	12592	Ri-Mark Platinum P 800 White		-	± 9003	= 700	= 9829-00	= 10	M7-100	800 PC	o10
62	12558	Ri-Mark Platinum P 863 Silver *K+AF		± 877 C	± 9006	= 735	= 9869-00	± 90	M7-190	836 PC	o90
63	12559	Ri-Mark Platinum P 864 Gold *K+AF		± 871 C	-	= 736	= 9879-00	± 93	M7-191	836 PC	-
64	12594	Ri-Mark Platinum P 899 Clear		-	-	= 740	= 9899-00	= 00	M7-105	840 PC	ooo
65	12560	Ri-Mark Platinum P 803 Black Matt *K+AF		± Black 3 U	-	= 721	= 9888-00	= 702	M7-111M	-	070 M
66	12561	Ri-Mark Platinum P 865 Anthracite Matt		-	-	-	= 9888-01	-	-	895 PC	o93
67	12595	Ri-Mark Platinum P 866 Silver Matt		± 877 U	-	-	= 9868-00	-	M7-195	891 PC	-
68	12596	Ri-Mark Platinum P 867 Copper Matt		-	-	-	= 9878-03	-	-	-	-
69	12597	Ri-Mark Platinum P 802 White Matt *K+AF		-	-	= 730	= 9828-00	102	M7-101M	830 PC	010 M
70	12598	Ri-Mark Platinum P 898 Clear Matt		-	-	-	= 9898-00	-	-	-	-
71	12776	Ri-Mark Platinum P 801 Black Airflow		± Black C	± 9005	-	= 9889-00 BF	-	M7A-110	-	-
72	12777	Ri-Mark Platinum P 800 White Airflow		± Black 3 U	± 9003	-	= 9829-00 BF	-	M7A-100	-	-

*K+AF= Available with Kraft liner and Airflow liner